


AT04-12PA-KIT01 12-WAY PIN RECEPTACLE, WEDGE AND CONTACTS KIT

PART NUMBER: AT04-12PA-KIT01

DATASHEET: View / Download

SPECIFICATIONS:

Amps: 13
AWG: 14-20
Color: Grey /Green
Contact Size: 16
Contact type: Pin
Dielectric Value: 1500V minimum
Housing Material: Thermoplastic
Insulation Resistance: 1000 megohms at 25°C
IP Rating: IP67
Mating Cycle Durability: >100
Positions: 12-Way A Position Key
Seal Diameter: .088" - .145"
Seal Material: Silicone Rubber
Temperature Range: -55°C TO +125°C
Wire Range: 14-20 AWG

QUANTITY

1 REQUEST A QUOTE

Like Sign Up to see what you friends like.
Like Sign Up to see what you friends like.

DESCRIPTION

12-Way Pin Receptacle, Wedge and Contacts Kit

Downloaded from Arrow.com.

RELATED ITEMS



AT04-12PA 12-Way Receptacle, Male, A Position Key, Extended Shroud. Compatible to part # DT04-12PA



AT04-12PA-BLK 12-Way Receptacle, Male, A Position Key, Extended Shroud, Black. Compatible to part # DT04-12PA-E004



AT04-12PA-EC01 12-Way Receptacle, Male, A Position Key, Extended Shroud, Enhanced A Key and End Cap. Compatible to part # DT04-12PA-BE02



AT04-12PA-ECBLK 12-Way Receptacle, Male, A Position Key, Extended Shroud, Enhanced A Key and End Cap, Black. Compatible to part # DT04-12PA-BE03



AT04-12PA-KIT01 12-Way Pin Receptacle, Wedge and Contacts Kit



AT04-12PA-MM01 12-Way Receptacle, Male, A Position Key, Extended Shroud, Reduced Diameter Seal (E-Seal), End Cap. Compatible to part # DT04-12PA-CE01



AT04-12PA-MMBLK 12-Way Receptacle, Male, A Position Key, Extended Shroud, Enhanced A Key , End Cap and Reduced Diameter Seal (E-Seal), Black. Compatible to part # DT04-12PA-BE04



AT04-12PA-NES 12-Way Receptacle, Male, A Position Key, Non-Extended Shroud



AT04-12PA-PM01 - 12-Way Flange Mount Receptacle



AT04-12PA-RD01 12-Way Receptacle, Male, A Position Key, Extended Shroud, Reduced Diameter Seal (E-Seal). Compatible to part # DT04-12PA-C015



AT04-12PA-SR2GRY - 12-Way Receptacle Male Connector with Reduced Seal, Position A



AT04-12PA-SR2GY 12-Way Receptacle Male Connector with Strain Relief and Endcap, Reduced Seal, A Position Key

Downloaded from Arrow.com.



AT04-12PA-SRGRY 12-Way Receptacle Male Connector with Strain Relief and Endcap, Standard Seal, Position A. Compatible to part # DT04-12PA-E008



AT04-12PA-SS01 12-Way Receptacle, Male Connector with A Position Key and Extended Shroud and Solid Rear Grommet and Endcap. Compatible to part # DT04-12PA-C017



AT06-12SA 12-Way Plug, Female, A Position Key. Compatible to part # DT06-12SA



AT06-12SA-BLK 12-Way Plug, Female, A Position Key, Enhanced Seal Retention (P012), Black. Compatible to part # DT06-12SA-EP07



AT06-12SA-EC01 12-Way Plug, Female, A Position Key, End Cap. Compatible to part # DT06-12SA-E003



AT06-12SA-ECBLK 12-Way Plug, Female, A Position Key, End Cap, Black. Compatible to part # DT06-12SA-E005



AT06-12SA-KIT01 12 Socket Plug, Wedge and Contacts Kit



AT06-12SA-MM01 12-Way Plug, Female, A Position Key, Reduced Diameter Seal (E-Seal), End Cap. Compatible to part # DT06-12SA-CE01



AT06-12SA-MMBLK 12-Way Plug, Female, A Position Key, Reduced Diameter Seal (E-Seal), Enhanced Seal Retention (P012), End Cap, Black. Compatible to part # DT06-12SA-CE11



AT06-12SA-RD01 12-Way Plug, Female, A Position Key, Reduced Diameter Seal (E-Seal). Compatible to part # DT06-12SA-C015



AT06-12SA-SR2GY 12-Way Plug with Strain Relief and Endcap , Female, A Position Key, Reduced Diameter Seal (E-Seal), Compatible to part # DT06-12SA-CE04



AT06-12SA-SRGRY 12-Way Plug Female Connector with Strain Relief and Endcap, Standard Seal, Position A. Compatible to part # DT06-12SA-E008









Downloaded from Arrow.com.

AT06-12SA-SS01 12-Way Plug, Female Connector with A Position Key and Solid Rear Grommet and Endcap, Wedgelock included. Compatible to part # DT06-12SA-C017

AT12PS-CKIT 12-Way Pin and Socket Plug, Receptacle, Wedge and Contacts Kit

AW12P - 12-Way Wedgelock Receptacle, Compatible to part # W12P

AW12S 12-Way Wedgelock Plug, Compatible to part # W12S



A Series Thermoplastic Connectors Catalog

BROWSE SIMILAR ITEMS

- Our Product Lines > A Series > AT Series > 12-Way Receptacles
- Market Applications > Heavy Equipment > Construction > A Series > AT Series > 12-Way Receptacles
- Market Applications > Heavy Equipment > Transportation > A Series > AT Series > 12-Way Receptacles
- Market Applications > Heavy Equipment > Off Road Recreation > A Series > AT Series > 12-Way Receptacles
- Market Applications > Automotive > Diagnostics > A Series > AT Series > 12-Way Receptacles
- Market Applications > Water Resistant - Waterproof > A Series > AT Series > 12-Way Receptacles
- Market Applications > Harsh Environments > A Series > AT Series > 12-Way Receptacles

Copyright 20182018 Amphenol Sine Systems. All Rights Reserved. eCommerce Software by 3dcart.

Downloaded from Arrow.com.