

GLCB35A1B-5

[Products](#) > [Switches](#) > [Limit Switches](#) > [General Purpose Limit Switches](#) > [GLC Series](#) > **GLCB35A1B-5**

Overview

MICRO SWITCH GLC Series Global Limit Switches, Side Rotary With Roller (shaft to back of switch), 2NO Slow Action, PG13.5, Gold Contacts. ...
[View More](#)



Technical Specifications

Availability	Global	Operating Force (OF)	0,12 Nm [1.10 in lb]
Pretravel (PT)	26°	Overtravel (OT)	49°
Differential Travel (DT)	11.5°	Product Type	EN50041/47 Global Limit Switch
Actuator	Side Rotary	Termination Type	PG13.5
Circuitry	2NO Slow action	Supply Voltage	1.0 Vac/Vdc to 50.0 Vac/Vdc

[View More](#)

View documents in: English ▾

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 MICRO SWITCH GLC, GLD, & GLE Series Miniature Global Limit Switches	Datasheet	English	15MB
 MICRO SWITCH Limit Switches Comparison	Product Range Guide	English	460KB
 Sensors and Switches in Mobile Cranes	Application Note	English	2MB
 MICRO SWITCH Limit Switches: Keep Trains Moving on Track	Application Note	English	1MB

[View More](#)

Product Features

- Designed to IEC standard for world-wide applications
- Certified for global applications: UL/CSA (Americas/Canada), CE (Europe), CCC (Asia-Pacific)¹
- International conduit sizes
- Direct PLC interface compatible (two circuit)
- Modular construction reduces maintenance parts costs
- Designed for ease of installation
- Variety of basic switch versions



view all GLCB35A1B-5 literature



view distributor inventory



sample request



email support



get support



email sales



find a distributor



email this page

- Wide choice of actuators
-
- ¹CCC certification is not available on the GL Series Switches sold within Europe, Middle East, and Africa. Option for CCC certification in these regions is available upon request.

Applications

- Machine tools: metal fabrication equipment, presses, transfer lines and special machinery
- Material handling equipment: conveyors, elevators, cranes, and hoists
- Packaging machinery and process equipment
- Textile machinery
- Construction machinery and equipment, vehicles and lift trucks

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.