Specification Sheet

Part Number: 161-64002



An innovative coupling system allows for an unlimited number of bundling combinations.

Clips can be easily released and reused.

Clips swivel freely which reduces mechanical stress and eliminates pinch points.

High Impact Polyamide 6.6 material provides firm fit even in rugged conditions.

Consists of acrylate adhesive with base of polyurethane foam allowing it to adhere firmly and easily to nearly any surface.

Helawrap, Accessory Clip, HWCLIP08, 5/16" Dia, PA66HIRHS, Black, 50/pkg

Article Number	161-64002
Type	HWCLIP08
Color	Black (BK)
Quantity Per	pack
Product Description	The Helawrap cable management system is the flexible routing and protection solution for industrial, datacom and electrical applications. Clips can be joined to a base and another clip of any size. Different cable sizes can be bundled together, organized and protected flexibly and efficiently.

Downloaded from Arrow.com.

Short Description	Helawrap, Accessory Clip, HWCLIP08, 5/16" Dia, PA66HIRHS, Black, 50/pkg
Global Part Name	HWCLIP08-PA66HIRHS-BK
Fixation Method	Plug-in mounting
Diameter D (Imperial)	0.375
Diameter D (Metric)	9
Nominal Diameter (Imperial)	0.31
Nominal Diameter (Metric)	8.0
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	No
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to +105°C)

Downloaded from Arrow.com.

Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

Downloaded from Arrow.com.