HAMMOND

Quality Products. Service Excellence.

Mounting Rack Rails *URR Series*

Features

- Constructed in 12-gauge steel.
- Sold in pairs.
- EIA/TIA compliant drilled and tapped 10-32 holes.
- Rack **Mounting hardware** is sold separately.
- Cabinet mounting hardware is not included.
- Rails come included with a rack unit indicator.
- Rails can be used for 19", 23" and 24" rack mounting applications.
- Also compatible with **RB-2PW** wall rack and 24" wide **HWC** wall cabinet.
- Side of rail folded for rear support or accessory mounting.
- Finished in RAL9005 black powder paint finish.
- TAA-compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.

Accessories

- 10-32 Mounting Hardware

		Mounting Dimensions		
Part No.	Rack Units	Height	Width	Depth
URR2U	2U	3.50	0.62	1.50
URR3U	3U	5.25	0.62	1.50
URR4U	4U	7.00	0.62	1.50
URR6U	6U	10.50	0.62	1.50
URR8U	8U	14.00	0.62	1.50
URR10U	10U	17.50	0.62	1.50
URR12U	12U	21.00	0.62	1.50
URR14U	14U	24.50	0.62	1.50
URR16U	16U	28.00	0.62	1.50
URR18U	18U	31.50	0.62	1.50
URR21U	21U	36.75	0.62	1.50
URR24U	24U	42.00	0.62	1.50
URR27U	27U	47.25	0.62	1.50
URR36U	36U	63.00	0.62	1.50
URR45U	45U	78.75	0.62	1.50

Tags: **Rackrail**, **Mounting Rails**, **Thin Flange Rails**, **Rack Rails**

Data subject to change without notice

Downloaded from Arrow.com.

© 2025. Hammond Manufacturing Ltd. All rights reserved.

Downloaded from Arrow.com.