

This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.


The marking on this product doesn't contain environmental hazardous materials per Material Specification 55-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.

**FOR REFERENCE ONLY**



REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	APPROVED
AX1	EDSR#5341	UNAPPROVED REVISION	01/26/2015	Arron Lin
AX2	EDSR#5559	ADDED COLOR OPTION	05/07/2015	Roger Tsai

**NOTES:**

- MATERIAL:  
HOUSING: HIGH TEMPERATURE THERMAL PLASTIC, NYLON 66, UL94V-0, COLOR: OPTION.
- PACKING IS PER AMTA PACKING SPECIFICATION PKS-0001.
- THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS PER DIRECTIVE 2011/65/EU FOR RoHS COMPLIANT.



PART NO. G53H XX X CEU  
 NO. OF POSITIONS — | — | COLOR  
 1: NATURAL  
 2: BLACK



POS	A	B
02	3.96 ±0.20	8.7
03	7.92 ±0.20	12.6
04	11.88 ±0.20	16.6
05	15.84 ±0.20	20.5
06	19.80 ±0.20	24.5
07	23.76 ±0.20	28.6
08	27.72 ±0.20	32.5
09	31.68 ±0.20	36.5
10	35.64 ±0.25	40.4
11	39.60 ±0.25	44.4
12	43.56 ±0.25	48.4
13	47.52 ±0.25	52.3
14	51.48 ±0.25	56.3
15	55.44 ±0.25	60.2
16	59.40 ±0.25	64.2
17	63.36 ±0.25	68.2
18	67.32 ±0.25	72.1
19	71.28 ±0.25	76.1
20	75.24 ±0.25	80.0

TOLERANCE		APPROVALS		DATE	TITLE		Amphenol®			
X.		DRAWN	Aqua Chou	05/07/2015	G53H SERIES, SOCKET HOUSING FOR CRIMP TYPE 3.96MM PITCH		Amphenol Corporation Amphenol Taiwan Corporation			
X.X	±0.30	CHECKED	Roger Tsai	05/07/2015						
X.XX	±0.20	APPROVED	Roger Tsai	05/07/2015						
X.XXX	±0.10	UNLESS OTHERWISE SPECIFIED		DWG TYPE	PROJECT CODE		UNIT	SIZE	PART No.	
		CUST DWG	SKT	NA	A3		G53HXXXCEU			
							SCALE	SHEET	DWG No.	REV.
							NA	1 OF 1	G53HXXXCEU	AX2