

A

B

C



D

E

F

G

H



SEC:A-A

TERMINATION:

P1	P2	COLOR
1	4	BLACK
2	3	RED
3	2	GREEN
4	1	YELLOW

Extended Length ("L2")	Typical Retracted Length ("L1")
84.0 Inches - 96.6 Inches	18.5 Inches
2,133.6MM-2,752.64MM	469.9MM

Material:

- Plug Housing: Polycarbonate, clear
- Plug Terminal: 0.36"[0.14MM] Thick Phosphor Bronze
- Connector: 50μ" of Selective Gold Contact Plating
 - Area, Gold flash over the remainder
 - Over 2.54μm[.000100] thick nickel underplate
- Conductor(X4C): 26AWG (0.12X12) Bare Copper
- Insulation(X4C): PP6331 ID 0.95-1.0
- Jacke: PVC No UL 80 P
- Package: Individual PE Bag

[illegible]

Item No.	
----------	--

AT-C-26-4/4/W-7

	Title
--	-------

NON-UL 26 AWG (0.12X12)*4C, O.D.: 2.4*4.8MM,
Standard Plug, 50μ" of contact plating, WHITE

Drawing No.

rev00

Replace

Sheet

