







NOTES:
MATERIAL:
CONTACTS:BRASS T=0.25mm
INSULATOR:PBT+30%G.F. UL 94V-0
FRONT SHELL:BRASS T=0.30mm
BACK SHELL:SPCC T=0.30mm
SPRING:SPCC
MECHANICAL:
MATING:35N MA
WITHDRAWAL FORCE:10N MIN
DURABILITY:1500CYCLES MIN
ELECTRICAL:
CURRENT RATING1.5A
VOLTAGE RATING:30V
WITHSTANDING VOLTAGE:750V AC
CONTACT RESISTANCE:25mΩ MAX
INSULATION RESISTANCE:1000MΩ MIN
PLATING
CONTACTS:GOLD FLASH AND TIN OVER NICKEL PLATED
SHELL:NICKEL OVER ALL PLATING
ENVIRONMENTAL:
TEMPERATURE RANGE:-55°C TO+85°C



P.C.B LAYOUT

10/01/30	ING	EG-N1012072			A3			
09/12/29	BENDEE	EG-H12067	變更尺寸標注位置		A2			
DATE	DR.BY	ECN.NO.	DESCRIPTION	MARK	VER.			
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差參考表		CnC Tech,LLC						
				TITLE: USB 8P A/F 雙層DIP 90°雙彈片5U"成品				
X.X	±0.38	X.X° ±2.0°	APPD:	PRODUCT NO: 1001-004-01010				
X.XX	±0.25	X.XX° ±1.0°	CHECK:	DATE	SCALE	UNIT	TYPE	PAGE
X.XXX	±0.13	X.XXX° ±0.5°	DRAW:	2010.01.30	1:1	mm	CD	1 / 1