



LH28F640BFHE-PBTLDY

To [Request More Information](#) from Sharp Microelectronics of the Americas ...

Documentation

There are no matching documents for this product or criteria.

Can't find the document you are looking for? Please contact your local [Sharp Microelectronics representative](#) for assistance.

| | |
|----------------------------|-----------------------------------|
| Access Time: | 90ns |
| Description: | 64M,Smart,Bottom Boot Block, 60ns |
| Device ID: | B1H |
| Family: | LH28F640BFHE-PBTLDY |
| Flash Density: | 64 |
| Lead Frame Type: | Alloy 42 |
| Life cycle: | Sunset |
| New Part Name: | LH28F640BFHE-PBTL70A |
| Organization: | x16 |
| Package Type: | 48 TSOP |
| Plating Material: | SnPb |
| Process Size: | 0.18 |
| Read Supply Voltage (Vcc): | 3V |
| RoHS: | Yes |
| Status: | Not for New Design |
| Supply Style: | Dual |
| Temperature Range: | -40C 85C |
| Type: | Bottom Bootblock |