

Part Number : [1301250004](#)
Product Description : Wire Rope Festoon Car Flat
Series Number : 130125
Status : Active
Product Category : Festoons
Engineering Part Number : 5111



Documents and Resources

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

| | |
|----------------|----------------------------|
| Status | Active |
| Category | Festoons |
| Series | 130125 |
| Description | Wire Rope Festoon Car Flat |
| Component Type | Car - Intermediate |
| Product Name | Aero-Motive |
| Type | Wire Rope |
| UPC | 78678863132 |

Physical

| | |
|--------------------------------|-----------------------------|
| Cable Height - Maximum | 6.86mm (.270") |
| Cable Width - Maximum | 60.45mm (2.380") |
| Combined Cable Weight-Max./Car | 4.08kg (9.0 lb) |
| Depth | 51.40mm (2.024") |
| Duty | Light |
| Height | 127.00mm (5.000") |
| Length | 115.06mm (4.530") |
| Material - Metal | N/A |
| Material - Resin | Nylon |
| Material - Wheel | Steel - Sealed Ball Bearing |
| Net Weight | 220.445/g |
| Number of Cars | 1 |
| Packaging Type | Individual Carton |
| Saddle Radius | 35.05mm (1.380") |
| Thread Size | N/A |
| Travel Speed - Maximum | 121.92 mpm (400 fpm) |
| Wire/Cable Type | Flat |

This document was generated on May 20, 2026