

KLBUE CO 2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

With our wide range of KLBÜ shield connections, you can achieve flexible and self-adjusting shield contacting and ensure error-free plant operation.

General ordering data

Version	Clamping yoke, Clamping yoke for shield connection, Steel
Order No.	1752131001
Type	KLBUE CO 2
GTIN (EAN)	4032248064434
Qty.	10 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	41.6 mm	Depth (inches)	1.6378 inch
Height	18 mm	Height (inches)	0.7087 inch
Width	21.1 mm	Width (inches)	0.8307 inch
Mounting dimension - width	20 mm	Net weight	18.7 g

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-60 °C...85 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption		
REACH SVHC	No SVHC above 0.1 wt%		
Product Carbon Footprint	Cradle to gate	0.086 kg CO2 eq.	

Material data

Basic material	Steel	Colour	silver
UL 94 flammability rating	None		

System specifications

Version	For a shield connection	End cover plate required	No
Mounting rail	Busbar		

Additional technical data

Type of fixing	Snap-on	Installation advice	Direct mounting, Busbar
Explosion-tested version	No		

Conductors for clamping (rated connection)

Stripping length	18 mm	Type of connection	Spring connection
Number of connections	1	Cable diameter, max.	15 mm
Cable diameter, min.	4 mm	Connection cross-section, stranded, max.	15 mm ²
Connection cross-section, stranded, min. 4 mm ²			

Dimensions

Pitch in mm (P)	18.00 mm
-----------------	----------

General

Installation advice	Direct mounting, Busbar	Mounting rail	Busbar
---------------------	-------------------------	---------------	--------

Rating data

Rated cross-section	10 mm ²
---------------------	--------------------

Technical data

Classifications

ETIM 8.0	EC002020	ETIM 9.0	EC002020
ETIM 10.0	EC002020	ECLASS 14.0	27-25-01-20
ECLASS 15.0	27-25-01-20		