Part Number : 1300138078
Product Description : Mini-Change Receptacle, 5 Poles, 1/2" - 14 NPT Threads, Male (Straight) to 16 AWG Leads, 1.0m (3.28') Length
Series Number : 130013
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 1R5006A80M010



Documents and Resources

Drawings

1300138078_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead; Triphenyl-phosphate per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Connectors
Series	130013
Description	Mini-Change Receptacle, 5 Poles, 1/2" - 14 NPT Threads, Male (Straight) to 16 AWG Leads, 1.0m (3.28') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Single Ended (pigtail)
UPC	887191262673

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V AC/DC

Physical

Coupling Type	External Thread
Gender	Male
Keyway	Single
Length	1.0m
Material - Component	Zinc Die-Cast with Black Epoxy
Mounting Thread Size	1/2" - 14 NPT
Net Weight	133.000/g
Orientation	Straight
Panel Mount	Front
Poles	5

Downloaded from Arrow.com.

Temperature Range - Operating	-20° to +105°C
Wire/Cable Type	UL 1015
Wire Size (AWG)	16

Downloaded from Arrow.com.