

CUSTOMER PRINT


PART NUMBER: W8380-XPG-P-3XX

- NOTES:
1. ALL PARTS ARE BULK PACKED
 2. CONTACTS SHIPPED UNASSEMBLED
 3. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE


ASS'Y P/N	CABLE O.D.
W8380-XPG-P-3DC	DAISY CHAIN
W8380-XPG-P-311	.09-.14 [2.3-3.5]
W8380-XPG-P-315	.15-.17 [3.8-4.3]
W8380-XPG-P-318	.18-.20 [4.6-5.1]
W8380-XPG-P-321	.21-.23 [5.3-5.8]

ASS'Y P/N	NO. OF CONTACTS
W8380-2PG-P-3XX	(2) #16
W8380-3PG-P-3XX	(3) #16
W8380-4PG-P-3XX	(4) #16
W8380-5PG-P-3XX	(5) #16
W8380-XPG-P-3XX	


GROMMET SIZE
NUMBER OF CONTACTS




WIRE VIEW
W8380-2PG-P-3XX




WIRE VIEW
W8380-3PG-P-3XX



WIRE VIEW
W8380-4PG-P-3XX




WIRE VIEW
W8380-5PG-P-3XX




FACE VIEW
W8380-3PG-P-3XX SHOWN

IN-LINE CONNECTOR, MALE
MAT'L: UV PBT, BLACK





.073±.015
[1.8±0.4]
CONTACT
HEIGHT

GROMMET, DAISY CHAIN
FOR W8380-XPG-P-3DC
MAT'L: RUBBER, BLACK



(2-5) #16 PIN CONTACTS, CRIMP
MAT'L: GOLD PLATED COPPER ALLOY




Ø.375
[9.5]
TYP

Ø.250
[6.4]

Ø.125
[3.2]


Ø.188
[4.8]



Ø.475
[12.1]
TYP


.430
[10.9]
TYP

GROMMET
MAT'L: SANTOPRENE, BLACK




.688
[17.5]

BACKSHELL
MAT'L: UV PBT, BLACK



WIRE VIEW
W8380-3PG-P-3XX SHOWN



ASSEMBLED VIEW
FOR CUSTOMER REFERENCE

DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS UNLESS INDICATED

CUSTOMER APPROVAL		
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.		
APPROVED BY:		
DATE:		

RoHS COMPLIANT

A	MA	07-13-20	DRAWING CREATED PER PDR 16014-10					
REV	INIT.	DATE	DESCRIPTION					
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: MA		DATE: 07-13-20		 601 E. WILDWOOD VILLA PARK, IL 60181	
			CHECKED BY:					
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY:		TITLE: IN-LINE CONNECTOR ASSEMBLY (2-5) #16 PIN CONTACTS, CRIMP INSTA-CLICK™ MINI-CON-X STANDARD PRODUCT			
= CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			SCALE	SIZE	SHEET	CUSTOMER:		
			NTS	B	1 OF 1			
▶			FILE:	DIRECTORY:	PART NUMBER:	REV A		
			W8380-XPG-P-3XX	SLW	W8380-XPG-P-3XX			