Part Number : 430315007
Product Description : Micro-Fit TPA Crimp Terminal, Male, with Tin (Sn) Pre-plated Phosphor Bronze Contact, 30-26 AWG, Reel
Series Number : 43031
Status : Active
Product Category : Crimp Terminals
Packaging Alternative : 430315017 (Bag)



Documents and Resources

Drawings

430315007_sd.pdf

PK-43031-001-001.pdf

STEP AP242

SOLIDWORKS

Creo

Specifications

436500001-PS-JA-000.pdf

436500001-PS-KO-000.pdf

436500001-PS-SP-000.pdf

PS-43650-001.pdf

430450005-TS-000.pdf

430450007-TS-000.pdf

TS-43045-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

Downloaded from Arrow.com.

REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	43031
Description	Micro-Fit TPA Crimp Terminal, Male, with Tin (Sn) Pre-plated Phosphor Bronze Contact, 30-26 AWG, Reel
Application	Wire-to-Wire
Product Name	Micro-Fit TPA
UPC	889056917216

Electrical

Current - Maximum per Contact	4.5A

Physical

Durability (mating cycles max)	30
Gender	Male

Downloaded from Arrow.com.

Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.061/g
Packaging Type	Reel
Plating min - Mating	1.000µm
Plating min - Termination	1.000µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.27mm max.
Wire Size (AWG)	26, 28, 30
Wire Size mm^2	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Micro-Fit TPA Single Row Plug Housings	200875

Application Tooling

Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	11030043
Hand Crimp Tool for Micro-Fit+ and Micro-Fit TPA Crimp Terminals, 26 AWG, UL1007 and UL1061 Wires	2133094800
Hand Crimp Tool for Micro-Fit+ and Micro-Fit TPA Crimp Terminals, 28 AWG, UL1007 and UL1061 Wires	2133094900
Hand Crimp Tool for Micro-Fit+ and Micro-Fit TPA Crimp Terminals, 30 AWG, UL1007 and UL1061 Wires	2133095000

Downloaded from Arrow.com.

Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp Terminals, 30-20 AWG	638120800
FineAdjust Applicator for Insulation OD 1.12-1.27mm, 30-26 AWG Wire	639004400
FineAdjust Applicator for Micro-Fit 3.0 Crimp Terminals, Insulation OD 0.63-1.10mm 30-26 AWG	639046600
T2 Terminator for Insulation OD 1.12-1.27mm, 30-26 AWG	639104400

Downloaded from Arrow.com.