

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

130102-0120

Status:

Active

Description:

Super-Safeway™ Rubber Hand Lamp with 100W Screw Release Reflector Guard with Switch and Side Outlet, Cord Length 15.24m (50.0'), Cord Type 16/3 SOOW



Documents:	
RoHS Certificate of Compliance (PDF)	Product Literature (PDF)
Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130102
NEMA Configuration	NEMA 5-15
Outlet	Side
Product Literature Order No	987650-8053
Product Name	Super-Safeway™
Type	Hand Lamps
UPC	78678879473
Woodhead	Yes
Physical	
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	No
Guard Type	Metal Wire
Height	374.65mm (14.750")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V
Material Info	
Old Part Number	106USB163

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130102Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION