

24-Port 1U Rack-Mount Cat6/Cat5 110 Patch Panel, 568B, RJ45 Ethernet, TAA

MODEL NUMBER: N252-024



Highlights

- 19-in. rackmount ready, 1U height (1.75")
- EIA/TIA 2/32 spacing
- 110 type punchdown termination
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Cat6 Patch Panel 568B- 24 Port, 1U

Description

Category 6 Patch Panels offer you all the functionality and compatibility as any name brand. Each panel comes with 110-type termination, while meeting and exceeding EIA/TIA TSB-40 Cat6 connecting hardware specifications. Color coded for both EIA/TIA 568A and 568B installations. 24 ports ensure a wide range of plug-n-play options. The clear numbering on both the front and back of each panel gives you a quick and easy way to identify cable runs and the high-density 19-inch panel design will save you valuable space in on the rack.

UTP Cat6 22-24 AWG solid cable

Features

- Cat6
- UL approved
- Ports clearly numbered both on front and back
- Labels on front enable each port to be named
- Color coded label on back offers both EIA/TIA 568A & 568B wiring
- Metal frame
- EIA/TIA 2/32 spacing
- Rack mountable on a 19 rack (1U of space)

Specifications

OVERVIEW	
UPC Code	037332120038
Product Type	Rackmount
Technology	Cat5/5e; Cat6
CONNECTIONS	

Number of Ports	24
Side A - Connector 1	110 IDC
Side B - Connector 1	RJ45 (FEMALE)
PoE Type	Type 2 PoE+ (30W, IEEE 802.3at)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	2.20 x 20.50 x 4.25
Shipping Dimensions (hwd / cm)	5.59 x 52.07 x 10.80
Shipping Weight (lbs.)	1.30
Shipping Weight (kg)	0.59
Panel Style	Punchdown
STANDARDS & COMPLIANCE	
Product Compliance	Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.