




**Part Number :** [2051960360](#)  
**Product Description :** Easy-On FFC/FPC Connector, 0.50mm Pitch, FV2R Series, Receptacle, Vertical, Dual Contact, 3.90mm Height, 7.10mm Mated Height, Gold (Au) Plating, 36 Circuits  
**Series Number :** 205196  
**Status :** Obsolete  
**Product Category :** FFC / FPC Connectors



## Documents & Resources

### Product Environment Compliance

#### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

#### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

### Part Details

#### General

Status	Obsolete
Category	FFC / FPC Connectors
Series	205196
Description	Easy-On FFC/FPC Connector, 0.50mm Pitch, FV2R Series, Receptacle, Vertical, Dual Contact, 3.90mm Height, 7.10mm Mated Height, Gold (Au) Plating, 36 Circuits
Series Name	FV2R
Product Name	Easy-On
UPC	191128794091

## Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V

## Physical

Actuator Type	Flexi-Latch
Circuits (Loaded)	36
Circuits (maximum)	36
Color - Resin	Black
Contact Position	Dual
Durability (mating cycles max)	20
Mated Height	7.10mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Polyester
Net Weight	426.500/mg
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Mounting	Surface Mount
PCB Retention	Yes
Pitch - Mating Interface	0.50mm
Polarized to PCB	Yes
Stackable	No

Temperature Range - Operating	-20° to +85°C
Wire/Cable Type	FFC/FPC

This document was generated on Apr 26, 2025