



Part Number : [15045504](#)

Product Description : 2.54mm SL Interim Clip, 50 Circuits, Polarized

Series Number : 70013

Status : Active

Product Category : Connector Accessories

Engineering Part Number : 70013-1050



Documents and Resources

Drawings

[015045504_sd.pdf](#)

[700130000-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-70400-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	70013
Description	2.54mm SL Interim Clip, 50 Circuits, Polarized
Component Type	Interim Clip
Product Name	SL
UPC	800753605251

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (Loaded)	50
Circuits (maximum)	50
Color - Resin	Black
Flammability	94V-0
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	4.579/g

Number of Rows	2
Packaging Type	Bag
Polarized to Mating Part	Yes

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
SL Single Row Crimp Housings and CPA Retainers	<u>70066</u>
SL Female Terminals	<u>70058</u>
SL Single Row Female Insulation Displacement Connector Assemblies	<u>70400</u>
SL Single Row Female Receptacles	<u>70430</u>
SL Dual Row Crimp Housings	<u>70450</u>

This document was generated on May 05, 2026