Part Number : 190740021
Product Description : Krimptite Steel Star Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Carton
Series Number : 19074
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : SRB-S-129-06



Documents and Resources

Drawings

190740021_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19074
Description	Krimptite Steel Star Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 6 (M3.5), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring
Type	Ring Terminal
UPC	800755072792

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.530/g
Packaging Type	Carton
Stud Size	6 (M3.5)

Downloaded from Arrow.com.

Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
Hand Crimp Tool	640031200
Crimp Head for the AT-200 Pneumatic Hand Tool	640071200

Downloaded from Arrow.com.