

**Part Number :** [1301020140](#)

**Product Description :** Super-Safeway Rubber Hand Lamp with 100W Open End Guard, with Receptacle

**Series Number :** 130102

**Status :** Active

**Product Category :** Lamps and Lights

**Engineering Part Number :** 110U



---

## Documents and Resources

---

### Product Environment Compliance

#### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	Lamps and Lights
Series	130102
Description	Super-Safeway Rubber Hand Lamp with 100W Open End Guard, with Receptacle
NEMA Configuration	N/A
Product Name	Super-Safeway
Type	Hand Lamps
UPC	78678860440

### Agency

CSA	LR85374
UL	E59251

### Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V

### Physical

Bulb Type	Incandescent
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	153.92mm (6.060")
Duty	Industrial
Guard Included	Yes
Guard Type	Open End
Height	311.66mm (12.270")

Lamp Type	A21
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	Side
Packaging Type	Carton

---

This document was generated on May 22, 2026