





Mating face according to MIL-C-24308 / DIN 41 652 / CECC 75301-802



Printed board layout (1,6 ± 0,2 thick)
View component side



09 66 552 6633	M3	2			
09 66 552 7633	M3	3			
09 66 552 5633	M3	0,76 µm Au			
09 66 552 6613	4-40 UNC	2			
09 66 552 7613	4-40 UNC	3			
09 66 552 5613	4-40 UNC	0,76 µm Au	31084	04/SEP/02	YT
Part number	screw-lock	Performance level	Mod.	Dat.	Name

Dat.	Name				
Detail.	04/SEP/02	YT			
Insp.					
Stand.					
HARTING EURL F-95972 Paris			TB 09 66 552 X6X3		
			Sub.		



All Dim. in mm
Orig. Size DIN A 4



D-Sub female angled 50 poles
with solder pins, screw-lock,
board lock and grounding pins

Maßstab/
Scale

1,5:1

Blatt/ Page

1