Part Number : 192150009
Product Description : VersaKrimp Butt Splice for 22-18 AWG Wire, Carton
Series Number : 19215
Status : Active
Product Category : Splices
Engineering Part Number : AS-345



Documents and Resources

Drawings

192150009_sd.pdf

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19215
Description	VersaKrimp Butt Splice for 22-18 AWG Wire, Carton
Product Name	VersaKrimp
Style	Standard
Type	Butt Splice
UPC	800755062410

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.798/g
Packaging Type	Carton
Temperature Range - Operating	149°C
Wire Size (AWG)	18, 20, 22
Wire Size mm^2	0.35-0.80

Application Tooling

Downloaded from Arrow.com.

Global

Description	Part Number
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm² - 0.5mm²	640030100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

Downloaded from Arrow.com.