



**Part Number :** [1300950294](#)

**Product Description :** Multi-Weave Wire Mesh Pulling Grip, Flexible Eye, Mesh Length 1.778m (70.00"), Approximate Break Strength 21772.43kg (48000 lbs)

**Series Number :** 130095

**Status :** Obsolete

**Product Category :** Cable Grips

**Engineering Number :** 36646



---

## Documents & Resources

---

### Product Environment Compliance

#### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

#### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Obsolete
Category	Cable Grips
Series	130095
Description	Multi-Weave Wire Mesh Pulling Grip, Flexible Eye, Mesh Length 1.778m (70.00"), Approximate Break Strength 21772.43kg (48000 lbs)
Comments	Color Identifier Dark Blue, Eye Cable Thickness 5/8"
Product Name	Multi-Weave
Type	Pulling Grip
UPC	78678836646

### Agency

CSA	LR32159
-----	---------

### Physical

Approximate Break Strength	21772.43kg (48000 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	44.45-56.90mm (1.750-2.240")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	1.778m (70.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A