C2G

Discontinued - 1ft (0.3m) Premium Shielded HD15 SXGA M/M Monitor Cable with 45° Angled Male Connector

Part No. 35010



Gain maximum flexibility in positioning your monitor with this angled connector cable. The 45° connector on one end of the cable allows installation in even the tightest locations. This premium VGA cable is ideal for video presentation devices, video splitters, and KVM switches. Constructed from premium grade video cable, it uses a combination of coax and twisted pair to accommodate cable runs up to 100 feet away without a booster (in most cases), and without the typical distortion problems associated with extended length cabling runs.

SXGA provides a screen resolution of 1280 x 1024 pixels.

Please Note: Pin 9 is not loaded. Pin 9 is not required for standard computer video applications.

Features & Benefits

- Supports up to a 1280x1024 resolution
- 45° connector for installations in tight spaces
- Coax and twisted pair construction

Specifications

General Info

Product Line	C2G	Color	Gray
UPC Number	757120350101	Country Of Origin	China
Application Sector	Commercial, Residential	Type	Cable

Dimensions

Cable Length	1 ft

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Video Resolution	SXGA (1280x1024)
Shielded/Unshielded Cable	Shielded	Cable Type	Video
Jacket Rating	Standard / Non-Rated	Connector 2	VGA Male
Connector 1	VGA Male	Video Output Support	VGA
Video Input Support	VGA		

Downloaded from Arrow.com.