



NOTES:


1. ALL PARTS TO BE BULK PACKED.
2. CONTACTS ASSEMBLED INTO CONNECTOR.
3. PC TAIL LENGTH OPTIONS:
 - STANDARD (SHORT) TAIL = 0.107in [W4281-1XSG-300]
 - INTERMEDIATE = 0.202in [W4291-1XSG-300]
 - LONG = 0.267in [W4292-1XSG-300]
4. ALL DIMENSIONS ARE REFERENCE ONLY
EXCEPT WHERE NOTED WITH A TOLERANCE.
DIMENSIONS IN BRACKETS [] ARE METRIC.




FACE VIEW
W4281-10SG-300
10-POS.



FACE VIEW
W4281-11SG-300
11-POS.






FACE VIEW
W4281-12SG-300
12-POS.





PC TAIL LAYOUT

**RECOMMENDED
PANEL CUTOUT**
STANDARD MULTI-CON-X



PC TAIL VIEW
W4281-10SG-300 - 10-POS. (11&12 CLOSED)
W4281-11SG-300 - 11-POS. (12 CLOSED)
W4281-12SG-300 - 12-POS. (ALL OPEN)



CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT / INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____
DATE: _____

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1
REV.	INIT.	DATE	DESCRIPTION
ORIG. DRAWN BY: PAK 10/03/14			DATE: 10/03/14
CHECKED BY:			
APPROVED BY:			TITLE: PANEL SOCKET, E-KEY
			12-POS., #20 PC TAIL, SHORT (STD.)
			MULTI-CON-X, WEATHER RESISTANT
			CUSTOMER: STANDARD PRODUCT
FILE: W4281-1XSG-300	DIRECTORY: SLW	REV: A	PART NUMBER: W4281-1XSG-300

CONXALL
601 E. WILDWOOD VILLA PARK, IL 60181

TITLE: PANEL SOCKET, E-KEY
12-POS., #20 PC TAIL, SHORT (STD.)
MULTI-CON-X, WEATHER RESISTANT

CUSTOMER: STANDARD PRODUCT

FILE: W4281-1XSG-300

DIRECTORY: SLW

REV: A