

You are here: Home

- Home
- Surface Mount Products ▶
- X2Y Products ▶
- Leaded Capacitors ▶
- High Temp Capacitors ▶
- Technical Notes ▶
- Prototyping Kits ▶
- View Product Catalog
- Product Training
- Environmental Compliance ▶
- Distributor Inventory

Match Info	Matching Parts and Available Actions:	
2450DP15D5400E Offsite Match	▣ Diplexers EIA 0603-2520, 859 MHz - 2450 MHz Links will send you to our partner company, Johanson Technology Search Distributor Inventory	Datasheet

Part Number Search

Parameter Search



About

- Contact Info
- Company Info
- Sales Rep
- Distributors
- Careers
- RoHS Compliance

Technical Notes

- General
- Application Notes
- Processing
- Environmental
- X2Y Applications
- Product training

Products

- Surface Mount
- X2Y technology
- Prototyping Kits
- Leaded Capacitors
- High Temp Capacitors
- Full Product Catalog

Support

- Quote Request
- Sample Request
- Prototyping Kit Request
- Hard literature Request
- Ask a Technical Question
- Purchasing Terms and Conditions

Johanson Dielectrics
johansondielectrics.com
15191 Bledsoe St.
Sylmar, CA 91342
818-364-9800 phone
818-364-6100 fax