

Quick Links
<a href="#">Cross reference</a>
<a href="#">RoHS/LF P/N Search</a>
<a href="#">Industry Standards</a>
<a href="#">Alphabetical List</a>
<a href="#">Documentation</a>
<a href="#">3D model search</a>
<a href="#">Customer drawing search</a>
<a href="#">Multi Selection Search</a>
<a href="#">Search by category</a>

Start > Search=VK20725000JOG\* > VK20725000JOG

**VK20725000JOG**

**VK20725000JOG - Terminal Blocks : Pluggable socket (male header), 5.0mm pitch, with flange, 45 degree, 20 position**



ACTIVE

Distributor Stock

[Print Datasheet](#)

FCI Brings You More  
[Contact our sales/technical support](#)  
[Sample request](#)

[Customer drawing](#) [Environmental Compliance Report](#)

[Specifications](#) [Download document](#)

General	Dimensional	Electrical	Mechanical	Physical	Approvals / Certifications	Mounting
<b>General</b>						
Gender					Socket (male header)	
Orientation					45 Degree	
Packaging					Box	
Product Type					Pluggable Socket	
Series					VK	
Number of Positions					20	
<b>Dimensional</b>						
Pitch					5.0 mm	
<b>Electrical</b>						
Withstanding Voltage					1.6 kV	
Current rating					15 A	
Voltage rating					300 V	
<b>Mechanical</b>						
Number of mating cycles					200	
<b>Physical</b>						
Soldering temperature (celcius)					260 +/- 5 Celcius (5 sec)	
Color (Housing)					Green	
Material (Housing)					Thermoplastic UL94V-0	
Terminal material					Copper	
Terminal plating					Tin	
Temperature (Operating - range)					-40 to +115 Celcius	
<b>Approvals / Certifications</b>						
Approvals / Certifications					cULus, VDE, TUV	
<b>Mounting</b>						
Board attachment					TMT	

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.