

Part Number : [468180001](#)

Product Description : EXTreme Guardian Crimp
Harness Housing, 3 Circuit, 11.00mm Pitch, 10-8 AWG

Series Number : 46818

Status : Obsolete

Product Category : Connector Housings



Documents and Resources

Drawings


[468180001_sd.pdf](#)

Specifications

[PS-46819-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	46818
Description	EXTreme Guardian Crimp Harness Housing, 3 Circuit, 11.00mm Pitch, 10-8 AWG
Application	Wire-to-Board, Wire-to-Wire
Product Name	EXTreme Guardian
UPC	883906730963

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	3
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Material - Resin	Polyester
Net Weight	15.840/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	11.00mm
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
EXTreme Guardian Power Plug Assemblies	<u>46817</u>

Use with Part(s)

Description	Part Number
EXTreme Guardian Female High Power Terminals	<u>46819</u>

This document was generated on Apr 12, 2026

Obsolète