

Home: > **Datasheet**

Part Number: 87898-0552

2.54mm SRSW SMT Hdr W/CapT&R .05AuLF5Ckt

Status: Active
Series: 87898
Category: Molex Parts

 CHECK DISTRIBUTOR INVENTORY [Add to My Parts](#)

Go to **Part Detail**▼

Series image - Reference only

Specifications & Other Documents:

Documents not available online

Sales Drawings, 3D Models, and Brochures

Documents not available online

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU RoHS: ELV and RoHS Compliant

China RoHS: 

REACH SVHC: Contains SVHC: No

Low-Halogen Status: Not Low-Halogen

Part Detail

COLLAPSE ALL

▼ General

Status	Active
Category	Molex Parts
Series	87898
UPC	887191000824

▼ Physical

Flammability	94V-0
Net Weight	0.311/g

▼ Agency Certification

UL	E29179
----	--------

▼ Solder Process Data

Duration at Max. Process Temperature (seconds)	40
Lead-free Process Capability	Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260

▼ Material Info

Molex Connectors

Wire-to-Board
Board-to-Board
Wire-to-Wire
Input/Output (IO)
FFC/FPC
Sockets

Other Products

Fiber Optic Products
Antennas
Industrial Automation
Membrane Switches
Copper Flex
PCB Assemblies
Woodhead Electrical
Solid State Lighting

Resources

- Catalog
- Cross-Reference
- Industries
- Literature
- Product Name

Company Info

- About Us
- Careers
- Contact Us
- ecocare
- Investors
- Press Room
- Shows & Events

Other Info

Feedback
Help
Legal Disclaimer
Privacy Policy
Sitemap

Stay Connected with Molex:

