T 3394 528 U





Data Overview

Description:	Male Plug; 5s Pin; Solder; Gold; 6-8mm; IP40
rated voltage	100 V
number of positions (w/o PE)	5
rated current (40 °C)	7 A
termination	solder pin
contact plating	gold
IP-class mated	IP40
Product Availability	Currently not on stock
Packing Unit:	**50 Pieces**
Min. Order Quantity:	**100 Pieces**
Price per Piece:	**€4.70**
Total Price plus VAT:	**€470.00**

Send Request

100 Add to Cart

Stock of our Distributors

Technical Data

- General Characteristics
- Electrical Characteristics
- Further Characteristics
- Downloads

Frequently Asked Questions

- Which components belong to a complete bill of materials (BOM)?
- Amphenol as a supplier of complete assemblies and plug & play solutions
- What options are there for direct transfer to a printed circuit board?
- How does the transmission of the cable shielding work with M16B connectors?
- Crimping or soldering - what are pros & cons?
- Tarnishing of silver-plated contacts - what's the reason?
- What options are there for color adjustments to the application?
- M16 receptacles with hex nut instead of ring nut?
- What are the 5 and 7 pole stereo layouts used for?
- What does the U at the end of the part number stand for?

This might interest you



Accessory »



Housing »

Disclaimer: No liability is accepted for the correctness and completeness of the suggested accessories.

Newsletter

E-Mail

I would like to receive the newsletter on the latest products, current trade fairs and promotions and give the following consent.

Subscribe to Newsletter

© Amphenol Tuchel Industrial GmbH 2026

Downloaded from Arrow.com.