

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0797582068

Status:

Active

Overview:

Off-the-Shelf Pre-Crimped Leads

Description:

Pre-Crimped Lead High-Power MultiCat Female-to-MultiCat Female, Gold (Au) over Nickel Phosphorus (NiP) Plating, 300.00mm Length, 12 AWG, Black

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Datasheet (PDF)

General	
Product Family	Cable Assemblies
Series	79758
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	MultiCat Crimp Terminals
Overview	Off-the-Shelf Pre-Crimped Leads
Product Name	MultiCat
UPC	191128292764
Physical	
Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel Phosphorus
Material - Plating Termination	Gold
Net Weight	8.565/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.30mm
Wire Size AWG	12
Wire/Cable Type	UL 1199
Electrical	
Current - Maximum per Contact	26.0A
Material Info	
Engineering Number	F30H1288L300
Reference - Drawing Numbers	
Sales Drawing	797582065-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

79758 Series

Use With

MultiCat High-Power Circular Receptacle Housing [200915](#) . MultiCat High-Power Inline Receptacle Housing [201841](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION