



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US



Search Panduit.com

GO



Search within category

GO

BUY NOW

DESIGN / INSTALL

PPMS1423B

NATURAL GAS

Pipe marker, 'NATURAL GAS' (legend), Yellow, Size B.

Sold in US and Canada only

Specs

Packaging Details

Documents



Add to Favorites



Add to BOM

Material	Coiled Rigid Vinyl
Overall Width (mm)	228.6
Overall Height (mm)	203.2
Note	Sold in US and Canada only
Application	Mark and identify contents in pipes and piping systems, including flow directions and hazard classification for maintenance and safety purposes. Pipe markers are designed in accordance to ASME (ANSI) A13.1 recommendations for sizes, colors, and visibility.
Color	Black/Yellow
Diameter (mm)	50.8
Dimensions (In.)	9" x 8"
Environment	1-2 years
Legend	NATURAL GAS
Maximum Operating Temperature (°C)	70
Maximum Operating Temperature (°F)	158
Maximum Overall Height (mm)	203.2
Minimum Operating Temperature (°C)	-20
Minimum Operating Temperature (°F)	-4
Part Features	Heavy-gauge 20-mil rigid vinyl plastic is pre-coiled to wrap and 'snap' fit completely around the pipe, Fits over pipes with dirty, greasy, or rough surfaces or other less than perfect areas - and easy to remove and place back with the memory coil shape, Printed repeatedly with the legend and directional flow arrow, upright and upside-down, around the marker, for universal directional fit and visibility from various angles, Fits pipe diameter 1.5" to 2"
Thickness (mm)	0.508
UL Listed	No
RoHS Compliancy Status	Compliant
Min. Order Qty.	1
Sub Brand	Stock Pipe Markers