



\*\*\*Spare part\*\*\* SIMATIC DP, Master-Modul IM 180 for PROFIBUS DP, max. 12 Mbaud

Figure similar

General information	
Suitability for use	Master applications
ASIC	ASPC2
<ul style="list-style-type: none"> <li>Scope of firmware</li> </ul>	80 KB
Supply voltage	
Rated value (DC)	5 V
Input current	
Current consumption, typ.	250 mA
Processor	
Processor type	80C165 (40 MHz)
Memory	
Type of memory	2x 128 KB
Interfaces	
Interfaces/bus type	Dual-port RAM
PROFIBUS DP	
<ul style="list-style-type: none"> <li>Transmission rate, max.</li> </ul>	12 Mbit/s
Protocols	
PROFIBUS DP	Yes
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> <li>min.</li> <li>max.</li> </ul>	0 °C 70 °C
Dimensions	
Width	100 mm
Height	100 mm

last modified: 2/13/2021