

Quick Links

Cross reference

RoHS/LF P/N Search

Industry Standards

Alphabetical List

Documentation

3D model search

Customer drawing search

Multi Selection Search

Search by category

Start > Search=10134348-001LF* > 10134348-001LF

10134348-001LF

10134348-001LF : Earth Screwless Terminal Block QE 2.5



ACTIVE

RoHS Compliant

Distributor Stock

 [Print Datasheet](#)

FCI Brings You More

 > [Contact our sales/technical support](#)

 > [Sample request](#)

 Customer drawing

 Environmental Compliance Report

Specifications

Download document

General	
Pollution Degree	3
Insulating Material Group	I
Number of contacts (Total)	2
Number of decks	Single
Packaging	Pack
Product Type	Spring Terminal Blocks
Attachment type (Board)	DIN Rail
Dimensional	
Width	5 mm
Conductor cross section solid (min-max)	1,0 / 4 sqmm
Conductor cross section stranded (min-max)	1,0 / 4 sqmm
Length (Overall)	53 mm
Strip length (Wire)	max 12 mm
Solid wire size (AWG)	24-12
Height (Total)	28,5 mm
Electrical	
Rated Surge Voltage	8kV
Surge Voltage Category	III
Current Rating (Max)	32 A
Physical	
Color (Housing)	Yellow/Green
Flammability rating	UL 94 V-2
Material (Insulator)	PA
Approvals / Certifications	
Approvals / Certifications	cURus
Mounting	
Mounting style	Omega TH 35

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.

Downloaded from [Arrow.com](#).