Part Number : 734153640
Product Description : MCX Plug, Right-Angle, Crimp, RG-179 Cable, Brass Body, Gold (Au) Plated, 75 Ohms
Series Number : 73366
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

734153640_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-89678-8590-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Plug, Right-Angle, Crimp, RG-179 Cable, Brass Body, Gold (Au) Plated, 75 Ohms
Application	RF
Product Name	MCX
Style	Cable
Type	Microminiature
UPC	800756588247

Electrical

Frequency	6 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	1.085/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A

Downloaded from Arrow.com.

Reverse Polar	No
Wire/Cable Type	RG-179

Solder Process Data

Lead-Free Process Capability	N/A

Downloaded from Arrow.com.