Data sheet

H10,0/15

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



For conductors from 10.0 to 185.0 mm² (AWG 7 - 350 MCM)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
• supplied loose in poly-bag

General ordering data

Version	Wire-end ferrule, Standard, 15 mm, 15 mm, No
Order No.	0124800000
Type	H10,0/15
GTIN (EAN)	4008190037475
Qty.	500 items
Packaging	loose

Downloaded from Arrow.com.

Data sheet

H10,0/15

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	0.37 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule without plastic collar	Version	Standard

Wire-end ferrules

Contact surface diameter (D1)	4.5 mm	Contact surface length (L2)	15 mm
Collar diameter (D2)	5.8 mm	L1 in mm	15.00 mm
Wire connection cross section AWG, max.	AWG 8	Stripping length	15 mm
Conductor cross-section	10 mm²		

Classifications


ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Downloaded from Arrow.com.