

Product data sheet

Characteristics

DDCC6-060

APC Data Distribution Cable, CAT6 UTP CMR
6XRJ-45 Black, 60FT (18.2M)



Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or Component Type	Network cable
Cable length	59.7 Ft (18.2 m)
Provided Equipment	User Manual
Product Compatibility	Patch Panel

Physical

Color	Black
Height	6.0 In (152 mm)
Width	13.5 In (343 mm)
Depth	13.5 In (343 mm)
Net Weight	13.80 Lb(US) (6.26 kg)
Mounting Mode	Not rack-mountable
Connector B	RJ45 female Cat Cat 6 Straight Through
Connector A	RJ45 female Cat Cat 6 Straight Through

Output

Number of port	6
----------------	---

Conformance

Product Certifications	TAA compliance[RETURN]UL Listed[RETURN]UL Recognized
------------------------	--

Environmental

Storage Relative Humidity	0...95 %
Storage altitude	0...10000 Ft (0...3048 m)
Ambient Air Temperature for Operation	5...113 °F (-15...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)

Ordering and shipping details

GTIN	731304252580
------	--------------

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	6.0 In (15.2 cm)
Package 1 Width	13.5 In (34.3 cm)
Package 1 Length	13.5 In (34.3 cm)
Package weight(Lbs)	14.79 Lb(US) (6.71 kg)

Environmental data

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is
Sustainable packaging	No
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
Take-back	Nej
WEEE Label	The product must be disposed on European Union markets following specific waste collection and neve

Contractual warranty

Warranty (in months)	24
----------------------	----

Product Life Status : **Commercialised**