

97 KHP3541/42-SW

Tools and harnessing machines



Knuckle-joint press for termination of RAST 2.5 connectors
in insulation displacement technology (IDT)

97 KHP3541/42-SW

Range of application

Connector	3541, 3542, 3541-1*, 3542-1*
Pole number	2-20
Pitch	2,5 mm
State of delivery of connectors	lose
Processable conductor	discrete conductor, notched flat cable 2.5 mm

Features

Application	low and middle volume production
Stroke capacity	ca. 400/h
Scope of functions and delivery	- Fixation of inserted discrete conductors by spring-loaded pressure pads until pressing
Options	- *Conversion kit for 3541-1 and 3542-1

Dimensions and supply data

Dimensions (H x W x D)	430 mm x 520 mm x 220 mm
Weight	ca. 25 kg

97 KHP3541/42-SW

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
KHP3541/42-SW	-		1