



Representative Image

## Catalog No. TY525M

**Description:** CABLE TIE 50LB 7 NAT NYLON 2-PC DI

**UPC No** 786210805092

**Home > Wire & Cable Management > Ty-Rap > Cable ties**

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 185.67mm (7.31 Inches), Width of 4.9mm (0.19 Inches), Thickness of 1.09mm (0.043 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds)

### Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

### Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	50 pounds , 222 newtons

### Classifications

Brand Name	Ty-Rap
Standard	UL E49405 UL E49405

### Dimensions

Width	0.19 in , 4.9 mm
Length	7.2 in , 183 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	0.12 to 1.89 in , 3 to 48 mm

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant