



Representative Image

Catalog No. 54160
Description: 2/0 CU STD BRL. 1 HOLE.5 INCH BOLT
UPC No 786210541600
Home > Connectivity & Grounding > Color Keyed / Blackburn > Cable or wire lug

Copper One-Hole Lug, Standard Barrel, Peep Hole, Max 35kV, Wire Size 2/0 AWG, 1/2 Inch Bolt Size, Tin Plated, Die Code 45, Die Color Code Black

Descriptors

Category	Cable or wire lug
----------	-------------------

Specifications

Cable Size	2/0 AWG
Number Of Holes	1
Voltage Rating	35 kV
Insulation	None
Material	Copper
Color	Black

Classifications

Brand Name	Color Keyed / Blackburn
Standard	UL E9809

Dimensions

Stud Size	1/2 in
-----------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	180° (horizontal)
Slender flange model	N
Insulated	N
With sight-hole	Y

ETIM	EC001051 Tube cable lug for copper conductors
Material	Copper
Surface protection	Tinned
Number of mounting holes	1
AWG size	Other

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	1097195_2015-02-20	N/A
CSA	7222	622302	N/A	N/A	N/A
UL	E9809	N/A	ZMVV	N/A	N/A