Part Number : 511030500
Product Description : 2.50mm Pitch, Mini-Lock Receptacle Crimp Housing, Single Row, Positive Lock, 5 Circuits, Natural
Series Number : 51103
Status : Obsolete
Product Category : Connector Housings



Obsolete

Documents and Resources

Specifications

511030000-PS-000.pdf
PS-51103-001-001.pdf
PS-51103-002-001.pdf
PS-51103-005-001.pdf
PS-51103-006-001.pdf
PS-51103-024-001.pdf
PS-51103-026-001.pdf
PS-51103-027-001.pdf
PS-51103-028-001.pdf
PS-51198-003-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Connector Housings
Series	51103
Description	2.50mm Pitch, Mini-Lock Receptacle Crimp Housing, Single Row, Positive Lock, 5 Circuits, Natural
Application	Wire-to-Wire
Product Name	Mini-Lock
UPC	800753574106

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	5
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle

Obsolete

Downloaded from Arrow.com.

Glow-Wire Capable	No
Keying to Mating Part	No
Material - Resin	Polyester
Net Weight	414.500/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini-Lock Single Row Plug Housings	51198
Mini-Lock Vertical Single Row Headers	53375
Mini-Lock Vertical Single Row Headers	53517

Use with Part(s)

Description	Part Number
Pre-Crimped Lead Mini-Lock Female-to-Mini-Lock Female, Tin (Sn) Plating, 150.00mm Length, 22 AWG, Black	797582147
Pre-Crimped Lead Mini-Lock Female-to-Mini-Lock Female, Tin (Sn) Plating, 300.00mm Length, 22 AWG, Black	797582148
Mini-Lock Female Crimp Terminals	50351

Obsolete

Downloaded from Arrow.com.