

MICRO SWITCH


A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
MINNEAPOLIS, MINNESOTA

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-RW84-A2



NOTE -
 ▲ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
 OF .139 MAX DIA ON 1.000 ±.002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE----- 3/4 OZ MAX

RELEASE FORCE----- 1/8 OZ MIN

DIFFERENTIAL TRAVEL----- .003-.015

OVERTRAVEL----- .219 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L103 15A 125, 250 OR 480 VAC
1/8HP 125 VAC, 1/4HP 250 VAC

L288
L299
L306



16A 250V ~ T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:

ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT .073 LB

CATALOG LISTING
BZ-RW84-A2
 PAGE 1 OF 1
M
 ISSUE 11
 REVISIONS
 A CO 16736 S C H 27 APRIL 62
 B CO 23645 M B F 23 JAN 68
 C CO-73287-J J A L 22 NOV 93
 D CO-77589 J A L 30 MAR 94
 E 203155 C S L 24 MAY 01
 RASTER
 0-30378
 DRAWN G C H 27 APRIL 62
 CHECK DAW 29 MAY 62
 REPLACES RELEASE NO.

MICRO SWITCH


A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
FREDERICK, MICHIGAN

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-RW84-A2



3X 6-32 UNC X (.219)
BINDING HEAD COMBINATION
TERMINAL SCREW AND
CUPWASHER

NOTE -

△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE----- 3/4 OZ MAX
RELEASE FORCE----- 1/8 OZ MIN
DIFFERENTIAL TRAVEL ----- .003-.015
OVERTRAVEL ----- .219 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

UNDERWRITERS' LAB. INC. LISTED RATING
-L103- 15 A-125, 250 OR 480 VAC
1/8 HP-125 VAC; 1/4 HP-250 VAC



SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.008
ANGLES ±

WEIGHT .073 LB

M BZ-RW84-A2

DRAWING NUMBER

ISSUE

RELEASE NO.

CHECK

REVISIONS

A	CO	116736	GCH	27 APRIL 62
B	CO	23645	M B F	23 JAN 68
C	CO-	73287-J	J A L	22 NOV 93
D	CO-	77589	J A L	30 MAR 94

CHECK

29 MAY 62

DAW

CHECK

27 APRIL 62

GCH

DRAWN

0-80378

Downloaded from Arrow.com