



- Circuit Board Indicators
- Panel Mount Indicators
- Solid State Lighting
- Traffic Signals
- Vehicle Lighting
- Rail
- Obstruction Lighting
- Hazardous Area Lighting
- Heliport Lighting

how to purchase

-  [sales contacts](#)
-  [stock check](#)

search

Product Line Search

Please select a Product Line to search.

Circuit Board Indicators

[find](#)

Part # / Text Search

Part No.:

Text Search:

[search](#)

quick links

Dialight Corporate Video

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives

Circuit Board Indicators - Through Hole Indicators


P/N# **5710101F**

2 mm Lens

Description	2 mm Bi-Level CBI X-R
Package Options	50 Pieces Per Bag
Product Type	Through Hole Indicators
Sub Product Type	with Bi-Level Housing
Configuration	2 mm Lens
Viewing	Right Angle
Viewing Angle	70
Test Current (mA)	10mA

Absolute Maximum Ratings (Ta = 25 °)

Solder Temp	260Å° for 5 sec
Operating Temp	-40 to +85° C
Storage Temp	-40 to +85° C



Operating Characteristics

LED Position	Found in position(s): 1	Found in position(s): 2
Color	Blank	Red
Lamp Type	Single Color	Single Color
LED Type		High Efficiency
Intensity Min (mcd)		8.0
Intensity Typ (mcd)		15.0
Intensity Max (mcd)		
Fwd Voltage Min		
Fwd Voltage Typ		
Fwd Voltage Max		
Dom Wavelength Min (nm)		625
Dom Wavelength Typ (nm)		
Dom Wavelength Max (nm)		
Power Dissipation Max (mW)		105
Backlighting		
Pitch Between Vertical		
Pitch Between Horizontal		
Lum Intensity Min		
Lum Intensity Typ		
Lum Intensity Max		

Distributor Stock Check

Check stock with our distributors now.

5710101F

[check stock](#)