



Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor


Home > Products Overview > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'CCS25-S8-C0'

Your search criteria matched only one product, shown below

CCS25-S8-C0



- Durable nylon cable clamps

	Part Number	CCS25-S8-C0
	RoHS Compliancy Status	Compliant
	Part Description	Fixed Diameter Cable Clamp
	Product Type	Mounting Device
	Material	Weather Resistant Nylon 6.6
	Color	Black
	UL Recognized	E136577
	Diameter (In.)	.17
	Diameter (mm)	4.2
	Width (In.)	.37
	Width (mm)	9.4
	Bundle Offset (mm)	10.4
	Bundle Offset (In.)	.41
	CE Compliant	No
	CE Marking	No
	Environment	Indoors/Outdoors
	Flammability Rating	UL94 V-2
	Max. Bundle Diameter (In.)	.25
	Max. Bundle Diameter (mm)	6.3
	Mounting Method	#8 (M4) Screw
	Pricing Description	Fixed Dia Clamp, .25" (6.4mm) Bundle, #8 Screw (M4), BL
	Screw Size Metric	M4
	Min. Order UOM	PC
	Min. Order Qty.	100
	BOM Qty. (# of Pkgs.)	0
	Add to Favorite Product List	e

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.