



**Part Number :** [1301500058](#)

**Product Description :** 20 Amp Safeway Pin and Sleeve Receptacle with Flip Lid, 2 Pole/3 Wire, 250V, Blue

**Series Number :** 130150

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** 320R6

---

## Documents and Resources

### Drawings

[1301500058\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Not Relevant                                  |
| China RoHS         | Not Reviewed per SJ/T 11365-2006              |
| EU ELV             | Not Relevant                                  |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21               |
| REACH SVHC         | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS            | Not Reviewed per EU 2015/863                  |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

|                    |   |
|--------------------|---|
| Status             | Active  |
| Category           | Wiring Devices  |
| Series             | 130150  |
| Description        | 20 Amp Safeway Pin and Sleeve Receptacle with Flip Lid, 2 Pole/3 Wire, 250V, Blue |
| Comments           | IEC Configuration 309-1/309-2   |
| IP Rating          | IP44  |
| NEMA Configuration | N/A   |
| Product Name       | Safeway   |
| Specialty          | Pin and Sleeve  |
| Type               | Receptacle  |
| UPC                | 78678861338   |

#### Agency

|    |         |
|----|---------|
| UL | E145923 |
|----|---------|

#### Electrical

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 20.0A |
| GFCI                          | No    |
| Voltage - Maximum             | 250V  |

#### Physical

|           |        |
|-----------|--------|
| Cord Type | N/A    |
| Flange    | Yes    |
| Flip Lid  | Yes    |
| Gender    | Female |
| Length    | N/A    |

|                   |               |
|-------------------|---------------|
| Lighted Connector | No            |
| Locking Blade     | No            |
| Poles             | 2-pole/3-wire |
| Receptacle Type   | Single        |

---

This document was generated on Apr 11, 2026