SERIES TL 2243 SWITCHES

TACT SWITCHES - Dual



SPECIFICATIONS

Contact Rating:	50mA @ 12 VDC
Life Expectancy:	30,000 cycles
Contact Resistance:	100mΩ max.
Insulation Resistance:	100MΩ min. @ 100 VDC
Dielectric Strength:	250VAC
Actuation Force:	180 ±50 gf
Operating Temperature:	-20°C to 70°C
Travel:	0.25 +0.2mm / -0.1mm

FEATURES & BENEFITS

- Low profile
- Tactile feel
- Saves space on the PC Board

APPLICATIONS/MARKETS

- Telecommunications
- Consumer Electronics
- Audio/visual
- Medical
- Testing/instrumentation
- Computer/servers/peripherals

HOW TO ORDER


SERIES	MODEL NO.
TL	2243


Example Ordering Number
TL–2243


Specifications subject to change without notice.

TL 2243










P.C. MOUNTING



SCHEMATIC

Downloaded from Arrow.com.