An error occured while your request was computed

Overview | **Technical data** | Downloads

- Item properties
- Ambient conditions
- Packaging information
- Classifications
- Material data
- PCB data
- Standards and regulations

Item properties

Brief article description	Upper part of housing
Type	ME 22,5 OT-MSTBO KMGY FL IOVC
Order No.	1116371
Housing type	DIN rail housing
Type	Upper housing part for connectors with header
Mounting type	Latching with lower housing part

Back to top

Material data

Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0
Housing material	Polyamide

Back to top

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

Back to top

PCB data

Mounting position	Vertical (horizontal DIN rail)
Type of PCB mount	Latching

Back to top

Packaging information

Pieces per package	10
Denomination packing units	Pcs.

Back to top

Standards and regulations

Flammability rating according to UL 94	V0

Back to top

Classifications

eCl@ss

eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

Back to top

ETIM

ETIM 5.0	EC001031

Back to top

PHOENIX CONTACT

586 Fulling Mill Road
Middletown, PA 17057

(800) 888-7388

Ask a question

Find product experts

© 2019 PHOENIX CONTACT Terms and Conditions Data Protection Sitemap

Downloaded from Arrow.com.