

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430246

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Cordset, 14 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 7.62m (25.0'), NEMA L16-20, 3Ø 480V

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR6837

UL

E38085

General

Product Family

Wiring Devices

Series

130143

IP Rating

IP67

NEMA Configuration

NEMA L16-20

Overview

Watertite Extreme Wet-Location Wiring Solutions

Product Name

Watertite Extreme

Receptacle Type

Single

Specialty

N/A

Taxonomy

Wiring Devices

Type

Cordset

UPC

78678863036

Physical

Cord Grip Body Size

F3 3/4"

Flange

No

Flip Lid

No

Gender

Male-Female

Length

7.62m (25.0')

Locking Blade

Yes

Net Weight

126.000/kg

Poles

3-pole/4-wire

Electrical

Cord Type

12/3 SOOW

Current - Maximum per Contact

20.0A

GFCI

No

Lighted Connector

No

Voltage - Maximum

3Ø 480V

Material Info

Engineering Number

26W76A144



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION