


Rev	AWO #	Description	Date	Appr
-		RELEASED	8/11/05	

APPROVED: _____


DATE: _____ TITLE: _____







SEC A-A



SEC B-B

WIRE SIZE	CIRCUITS			
AWG	2	4~6	8~10	12~24
18	9 A	8 A	7 A	6 A
20	7 A	6 A	5 A	5 A
22	5 A	4 A	4 A	4 A
24	4 A	3 A	3 A	3 A

PART #	WIRE AWG	DIMENSIONS			
		C	D	E	F
DMH-A-C-F-R	22 ~ 24	.134 [3.4]	.130 [3.3]	.098 [2.5]	.090 [2.3]
DMH-B-C-F-R	18 ~ 22	.157 [4.0]	.177 [4.5]	.098 [2.5]	.090 [2.3]
DMH-C-C-F-R	16 ~ 18	.157 [4.0]	.177 [4.5]	.110 [2.8]	.106 [2.7]

SPECIFICATIONS:
Material:
Contacts: Brass
Plating:
Tin over Copper underplate overall
Electrical:
Operating voltage: 600 VAC max
Current rating: / Contact (See Chart)
Contact resistance: 10 mohms max
Environmental:
Lead free, RoHS compliant. RoHS COMPLIANT

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

APPROVALS		DATE
DRAWN	SS	8/11/05
CHECKED		
APPROVED		

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: CRIMP CONTACT, DMH SERIES
FEMALE, TIN PLATED, ON REELS

SIZE	PART NO.	REV.
X	DMH-X-C-F-R	-

REF: | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.