



+ CONNECTORS

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HOUSINGS



✓ Active

TE CONNECTIVITY (TE)
FUEL PUMP 6P PLUG ASSY JPT TYP
Econoseal

936159-1
TE Internal Number: 936159-1

EU RoHS Compliant
EU ELV Compliant

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire
Number of Positions 6
Centerline (Pitch) 5.3 mm [.209 in]
Sealable Yes
Hybrid Connector No

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

FUEL PUMP 6P CONN'R ASS'Y(JPT)
PDF (TIFF AVAILABLE)
English

CAD Files

3D PDF
PDF
3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Board, Wire-to-Device, Wire-to-Wire

Sealable Yes

Hybrid Connector No

Strain Relief No

Row-to-Row Spacing 3.2 mm [.126 in]

Configuration Features

Number of Positions 6

Number of Rows 3

Body Features

Color Brown

Body Material PBT GF

Mechanical Attachment

Terminal Position Assurance No

Polarized Yes

Housing Features

Centerline (Pitch) 5.3 mm [.209 in]

Dimensions

Width 25.4 mm [1 in]

Height 37.8 mm [1.4882 in]

Length 27 mm [1.0629 in]

Industry Standards

UL Flammability Rating UL 94V-2

Packaging Features

Packaging Quantity 50

Other

Connector Position Assurance Capable No
Serviceable No

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF