



Part Number : [734151103](#)

Product Description : MCX Jack, Right-Angle, PCB Receptacle, Surface Mount, Die Cast Body with Brass Insert, 0.25µm Nickel (Ni) Plating, Tape and Reel, 50 Ohms

Series Number : 73366

Status : Active

Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[734151103 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Jack, Right-Angle, PCB Receptacle, Surface Mount, Die Cast Body with Brass Insert, 0.25µm Nickel (Ni) Plating, Tape and Reel, 50 Ohms
Application	RF
Product Name	MCX
Style	PCB
Type	Microminiature
UPC	884982192263

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	1.591/g
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	No
Panel Mount Method	N/A

PCB Mounting	Surface Mount
PCB Thickness - Recommended	Various
Reverse Polar	No
Wire/Cable Type	N/A

This document was generated on Sep 17, 2025